



## BA10E516

by Burndy  
Catalog ID: BA10E516

Prop 65 Notice

TERMINAL-POLYVINYLCHLORIDE INSULATED, RING TONGUE, 5/16"  
STUD, 600 VOLTS MAX. 105° C MAX.

## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLU <sup>TM</sup>
Type	Ring Tongue
UPC	781810026496
UPC 12 Digit	7818100264966

### Dimensions

Dimension - Hole Size fraction	1/3
Dimension - Hole Size inch	0.33 in
Dimension - Length Overall inch	1.22 in
Dimension - Pad Width inch	0.53 in
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.40 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	500
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)