



BA10E6M

by Burndy
Catalog ID: BA10E6M

TERMINAL-POLYVINYLCHLORIDE INSULATED, RING , 600 VOLTS MAX.
105° C MAX.

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLU TM
Type	Ring Tongue
UPC	781810028841
UPC 12 Digit	7818100288411

Dimensions

Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.91 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#6
Dimension - Z inch	0.20 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)