



BA10EL6

by Burndy
Catalog ID: BA10EL6

Prop 65 Notice

TERMINAL-POLYVINYLCHLORIDE INSULATED, LOCKING FORK TONGUE, #6 STUD

Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLU TM
UPC	781810026885
UPC 12 Digit	7818100268855

Dimensions

Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - Length Overall inch	1.05 in
Dimension - Pad Width inch	0.28 in
Dimension - Stud Size inch	#6
Dimension - Z inch	0.26 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)