

## BA10EZ10

by Burndy  
Catalog ID: BA10EZ10

Prop 65 Notice

Polyvinylchloride Insulated Copper Fork Terminal, Stud size:10, Wire strip length:11/32".

Features: Flange Fork Tongue Design: Allows Fast Installation-Screw Only Has To Be Loosened For Termination, The Flanges On The End Of The Fork Terminal Aid In Preventing A Slightly Loose Terminal From Becoming Fully Disconnected From The Screw: Flanges Make Re-securing A Loose Terminal Easier, 600 V Maximum, 105 DEG C Maximum, Employs A Flanged Fork Tongue For Fast Installation And Security, Package: Bulk, Color Code: Yellow, Finish: Tin Plated, Temperature Rating: 105 DEG C Maximum, Insulation Diameter (maximum): 0.26 IN, Installation Tool: MR15, M8ND Tool With N10ET-23 Die



## Product Details

### General

|                                      |                                    |
|--------------------------------------|------------------------------------|
| Application                          | For Fast Installation And Security |
| Connector Type                       | Terminal - Fork                    |
| Feature - Barrel Style               | Shrouded                           |
| Insulation                           | Y                                  |
| Insulation Type                      | Vinyl                              |
| Material                             | Copper                             |
| Physical Attribute - Number of Holes | 1                                  |
| Physical Attribute - Tongue Type     | Flanged Fork                       |
| Plated                               | Y                                  |
| Plating Type                         | Tin - Electro Plated               |
| Sub Brand                            | VINYLUG                            |
| Trade Name                           | VINYLUG™                           |
| Type                                 | Flange Fork                        |
| UPC                                  | 781810026441                       |
| UPC 12 Digit                         | 7818100264411                      |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Hole Size fraction  | 1/5     |
| Dimension - Hole Size inch      | 0.20 in |
| Dimension - Length Overall inch | 1.09 in |
| Dimension - Pad Width inch      | 0.41 in |
| Dimension - Stud Size inch      | #10     |
| Dimension - Z inch              | 0.31 in |

### Conductor Related

|                                   |               |
|-----------------------------------|---------------|
| Conductor - Copper Str Size       | 12 AWG;10 AWG |
| Conductor - Copper Str Size Range | 12 AWG-10 AWG |

|                |               |
|----------------|---------------|
| Conductor Type | CU C Str-Size |
|----------------|---------------|

## Certifications and Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | Yes   |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM    |
| UL Listed                          | Yes   |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 500 |
|-----------------------|-----|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)