

# BA10EZ8

by Burndy  
Catalog ID: BA10EZ8

Prop 65 Notice

Copper Terminal, Flanged Fork Tongue, 12-10 AWG, #6-#8 Stud, Vinyl Insulated, Tin Plated.

Features: Flange Fork Tongue Design: Allows Fast Installation-Screw Only Has To Be Loosened For Termination, The Flanges On The End Of The Fork Terminal Aid In Preventing A Slightly Loose Terminal From Becoming Fully Disconnected From The Screw: Flanges Make Re-securing A Loose Terminal Easier, 600 V Maximum, 105 DEG C Maximum, Employs A Flanged Fork Tongue For Fast Installation And Security, Package: Bulk, Color Code: Yellow, Finish: Tin Plated, Insulation Diameter (maximum): 0.26 IN, Temperature Rating: 105 DEG C Maximum, Installation Tool: MR15, M8ND Tool With N10ET-23 Die



## Product Details

### General

Application	For Fast Installation And Security
Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Flange Fork
UPC	781810026458
UPC 12 Digit	7818100264588

### Dimensions

Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	1.01 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#8
Dimension - Z inch	0.26 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	500
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)