

BA14E14

by Burndy
Catalog ID: BA14E14

Prop 65 Notice

Copper Terminal, Ring Tongue, 16-14 AWG, 1/4" Stud, Vinyl Insulated.

Features: Expanded Insulation Support Accepts Standard And Large Wire Diameters: Lowers Inventory Requirements, Permits Greater Flexibility And Provides Insulation Support, Funnel Entry: Easy Wire Insertion, Manufactured Of Pure Electrolytic Copper: Provides Maximum Conductivity, Low Resistance And Ductility For Excellent Crimp Forming Properties, Deep V Groove Serrations In The Inner Barrel: Provides Added Holding Strength And Better Conductivity, Electro-Tin Plated: Provides Durable Long-Lasting Corrosion Resistance, 600 V Maximum, 105 DEG C Maximum, Installation Tool: Plier Type: Y10D, Y10-22 Tool, Ratchet: MR8-89-1, MR15, MR8-G96 Tool, Package: Bulk, Insulation Diameter (maximum): 0.18 IN, Color Code: Blue, Wire Strip Length: 13/64 IN, Wire Insulation Grip: No, Temperature Rating: 105 DEG C Maximum, Finish: Electro-Tin Plated



Product Details

General

Application	For Commercial, Light Duty Industrial Control and Power Circuit Applications
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electroplated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810026632

Dimensions

Dimension - Hole Size fraction	10/37 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	0.99 in
Dimension - Pad Width inch	0.40 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.36 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
-------------------------------	----------------------

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG; 14 AWG
Conductor - Copper Str Size Range	16 AWG-14AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)