

BA14E38

by Burndy
Catalog ID: BA14E38

Prop 65 Notice

Copper Terminal, Ring Tongue, #16-#14 Wire Size; 3/8 Stud; Vinyl Insulation.



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electroplated
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810091500

Dimensions

Dimension - Hole Size fraction	16/41 in
Dimension - Hole Size inch	0.39 in
Dimension - Length Overall inch	1.15 in
Dimension - Pad Width inch	0.53 in
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.45 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG; 14 AWG
Conductor - Copper Str Size Range	16 AWG-14AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)