

# BA14E4

by Burndy  
Catalog ID: BA14E4

Prop 65 Notice

Copper Terminal, Ring Tongue, #16-#14 Wire Size; #3-#4 Stud Size; Vinyl Insulation.



## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electroplated
Trade Name	VINYLU <sup>TM</sup>
Type	Ring Tongue
UPC	781810026595

### Dimensions

Dimension - Hole Size fraction	3/25 in
Dimension - Hole Size inch	0.12 in
Dimension - Length Overall inch	0.71 in
Dimension - Pad Width inch	0.22 in
Dimension - Stud Size inch	#4
Dimension - Z inch	0.17 in

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG; 14 AWG
Conductor - Copper Str Size Range	16 AWG-14AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

## Logistics

Minimum Pack Quantity	1000
-----------------------	------

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)