

# BA14E6M

by Burndy  
Catalog ID: BA14E6M

Prop 65 Notice

TERMINAL-POLYVINYLCHLORIDE INSULATED, RING , 600 VOLTS MAX.  
105° C MAX, TAPE MOUNTED



## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLU <sup>TM</sup>
Type	Ring Tongue
UPC	781810028971
UPC 12 Digit	7818100289711

### Dimensions

Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.74 in
Dimension - Pad Width inch	0.25 in
Dimension - Stud Size inch	#6
Dimension - Z inch	0.18 in

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

**Logistics**

Minimum Pack Quantity	2000
-----------------------	------

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)