

BA14EL8M

by Burndy
Catalog ID: BA14EL8M

Prop 65 Notice

Fork Tongue Terminal, 16-14 AWG, #8 Stud, Polyvinylchloride Insulated, Tin Plated.

LOCKING FORK TERMINAL, 8 STUD. BLUE VINYL INSULATED, MYLARRELEED. 16-14 AWG. INSTALL WITH TFM1D5, TFM1D5R TFM DIE DFM 2-1. WIRE STRIP LENGTH 1/4"



Product Details

General

Application	Terminal - Fork
Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Small Terminals
UPC	781810029350
UPC 12 Digit	7818100293500

Dimensions

Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	0.91 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#8
Dimension - Thread Size	-
Dimension - Z inch	0.26 in

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)