

# BA14EZ10

by Burndy  
Catalog ID: BA14EZ10

Prop 65 Notice

Copper Terminal, Flanged Fork Tongue, 16-14 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated.

Features: Flange Fork Tongue Design: Allows Fast Installation-Screw Only Has To Be Loosened For Termination, The Flanges On The End Of The Fork Terminal Aid In Preventing A Slightly Loose Terminal From Becoming Fully Disconnected From The Screw: Flanges Make Re-securing A Loose Terminal Easier, 600 V Maximum, 105 DEG C Maximum, Employs A Flanged Fork Tongue For Fast Installation And Security, Insulation Diameter (maximum): 0.18 IN, Package: Bulk, Color Code: Blue, Wire Insulation Grip: No, Finish: Electro-Tin Plated, Installation Tool: Plier Type: Y10-22 Tool, Ratchet: MR8-89-1 Tool, Temperature Rating: 105 DEG C Maximum



## Product Details

### General

Application	For Fast Installation And Security
Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Flange Fork
UPC	781810026588
UPC 12 Digit	7818100265888

### Dimensions

Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.96 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
-------------------------------	----------------------

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1000
-----------------------	------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)