

BA16E38

by Burndy
Catalog ID: BA16E38

Prop 65 Notice

TERMINAL-POLYVINYLCHLORIDE INSULATED, RING , 600 VOLTS MAX.
105° C MAX, 22-16 AWG, 3/8 STUD SIZE



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	VINYLU TM
Type	Ring Tongue
UPC	781810026724
UPC 12 Digit	7818100267244

Dimensions

Dimension - Hole Size fraction	16/41
Dimension - Hole Size inch	0.39 in
Dimension - Length Overall inch	1.15 in
Dimension - Pad Width inch	0.53 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.45 in

Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)