



BA16EZ2

by Burndy
Catalog ID: BA16EZ2

Prop 65 Notice

TERMINAL-POLYVINYLCHLORIDE INSULATED, FLANGED FORK TONGUE, #2 STUD SIZE

Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	VINYLU TM
Type	Flange Fork
UPC	781810026779
UPC 12 Digit	7818100267799

Dimensions

Dimension - Hole Size fraction	1/11
Dimension - Hole Size inch	0.09 in
Dimension - Length Overall inch	0.78 in
Dimension - Pad Width inch	0.17 in
Dimension - Stud Size inch	#2
Dimension - Z inch	0.23 in

Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)