



BA208

by Burndy
Catalog ID: BA208

Shim Stock and Adapter Sleeves

Product Details

General

Trade Name	BURNDYWeld®
Type	Tools & Accessories
UPC	781810405208
UPC 12 Digit	7818104052088

Dimensions

Dimension - Inside Diameter inch	0.140 in
Dimension - Length Overall inch	1 in
Dimension - Outside Diameter inch	0.203 in

Conductor Related

Conductor - Copper Solid Size	#8 AWG, #9 AWG, #10 AWG
Conductor - Copper Str Size	#9 AWG, #10 AWG
Conductor - Rod Size	#4 AWG Sol

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)