

BB024L9T14

by Burndy
Catalog ID: BB024L9T14

Prop 65 Notice

Flexible Copper Braid, 9.00 in, Flexible copper braid jumpers designed to take up linear expansion and contraction.

Made of flat extra flexible, tinned, pure copper braid, with unplated, seamless, pure copper ferrules formed into a rectangular shape on each end.



Product Details

General

Application	Flexible copper braid jumpers designed to take up linear expansion and contraction
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Sub Brand	BRAID
Type	B
UPC	781810552537
UPC 12 Digit	7818105525377

Dimensions

Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9.00 in
Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4

Electrical Ratings

Rating - Indoor Amperage	93
Rating - Outdoor Amperage	93

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)