



## BB048L9T14

by Burndy  
Catalog ID: BB048L9T14

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810552476
UPC 12 Digit	7818105524766

### Dimensions

Dimension - L Length Overall mm	229
Dimension - Length Overall inch	9
Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4

### Electrical Ratings

Amperage Rating	93 A
Rating - Indoor Amperage	150
Rating - Outdoor Amperage	150

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)