



## BB100L111D20G25TN

by Burndy  
Catalog ID: BB100L111D20G25TN

Prop 65 Notice

Flexible Copper Braid

### Product Details

#### General

|                     |               |
|---------------------|---------------|
| Connector Type      | Braid         |
| Material            | Copper        |
| Material - Ferrules | Y             |
| Plated              | Y             |
| UPC                 | 781810649534  |
| UPC 12 Digit        | 7818106495344 |

#### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 2824 mm  |
| Dimension - Length Overall inch | 111.2 in |

#### Electrical Ratings

|                 |       |
|-----------------|-------|
| Amperage Rating | 300 A |
|-----------------|-------|

#### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

#### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)