



BB100L12D81M16TN

by Burndy
Catalog ID: BB100L12D81M16TN

Flexible Copper Braid with Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	621945473126

Dimensions

Dimension - L Length Overall mm	325 mm
Dimension - Length Overall inch	12.81 in

Certifications and Compliance

Certification - CSA Approved	Yes
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)