



## BB100L142D73G21TN

by Burndy  
Catalog ID: BB100L142D73G21TN

Prop 65 Notice

Flexible Copper Braid with Tin Plated Ferrules

### Product Details

#### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	621945434523
UPC 12 Digit	6219454345233

#### Dimensions

Dimension - L Length Overall mm	3600 mm
Dimension - Length Overall inch	141.73 in

#### Electrical Ratings

Amperage Rating	300 A
-----------------	-------

#### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

#### Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)