



BB100L18D70G21TN

by Burndy
Catalog ID: BB100L18D70G21TN

Prop 65 Notice

Flexible Tin Copper Braid 17.50 inches long

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	621945443679
UPC 12 Digit	6219454436799

Dimensions

Dimension - L Length Overall mm	450 mm
Dimension - Length Overall inch	17.7 in

Electrical Ratings

Amperage Rating	300 A
-----------------	-------

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)