



BB100L24D60G21TN

by Burndy
Catalog ID: BB100L24D60G21TN

Prop 65 Notice

Tin Plated Copper Braid 23.60 inches long

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810649428
UPC 12 Digit	7818106494288

Dimensions

Dimension - L Length Overall mm	599 mm
Dimension - Length Overall inch	23.6 in

Electrical Ratings

Amperage Rating	300 A
-----------------	-------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)