

BD11D63G150LD

by Burndy
Catalog ID: BD11D63G150LD

Lead Plated Ferrules



Product Details

General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| Plating Type | Lead |
| UPC | 781810204405 |
| UPC 12 Digit | 7818102044055 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 296 mm |
| Dimension - Length Overall inch | 11.64 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 190 |
| Rating - Outdoor Amperage | 225 |

Certifications and Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)