



## BD120G183TN

by Burndy  
Catalog ID: BD120G183TN

Tin Plated Ferrules

### Product Details

#### General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810206966
UPC 12 Digit	7818102069666

#### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)