



BD120G283TN

by Burndy
Catalog ID: BD120G283TN

Tinned copper flexible braid 120"x0.94"x0.13"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810657911
UPC 12 Digit	7818106579111

Dimensions

Dimension - L Length Overall mm	3048
Dimension - Length Overall inch	120
Dimension - Width inch	0.94
Dimension - Width mm	24 mm

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)