



## BD24G272TN

by Burndy  
Catalog ID: BD24G272TN

Tin Plated Copper Braid 24 in Long

### Product Details

#### General

Connector Type	Braid
Material	Copper
UPC	781810567401
UPC 12 Digit	7818105674011

#### Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in

#### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)