



BD24

by Burndy
Catalog ID: BD24

Prop 65 Notice

Flexible Copper Braid, 24 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction, 24 IN L.

Made of flat extra flexible, tinned, pure copper braid, with unplated, seamless, pure copper ferrules formed into a rectangular shape on each end.

Product Details

General

Application	Flexible copper braid jumpers designed to take up linear expansion and contraction
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
Sub Brand	BRAID JUMPER
Type	B, Flexible
UPC	781810806999
UPC 12 Digit	7818108069999

Dimensions

Dimension - D inch	2.50 in
Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	0.94 in

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)