



BD40TN

by Burndy
Catalog ID: BD40TN

Tinned copper flexible braid 40"x0.94"x0.13"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810496411
UPC 12 Digit	7818104964111

Dimensions

Dimension - L Length Overall mm	1016
Dimension - Length Overall inch	40
Dimension - Width inch	0.94
Dimension - Width mm	24 mm

Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	7
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)