



BD60U

by Burndy
Catalog ID: BD60U

Undrilled and Tin Plated Tin Plated Copper Braid 60 in Long

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810526125
UPC 12 Digit	7818105261255

Dimensions

Dimension - L Length Overall mm	1524 mm
Dimension - Length Overall inch	60.00 in

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)