



## BD70TN

by Burndy  
Catalog ID: BD70TN

Tinned copper flexible braid 70"x0.94"x0.13"

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810496381
UPC 12 Digit	7818104963811

### Dimensions

Dimension - L Length Overall mm	1778
Dimension - Length Overall inch	70
Dimension - Width inch	0.94
Dimension - Width mm	24 mm

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	4
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)