



## BD9T14

by Burndy  
Catalog ID: BD9T14

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
UPC	781810552650
UPC 12 Digit	7818105526500

### Dimensions

Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9.00 in
Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)