



BDALHC16500

by Burndy
Catalog ID: BDALHC16500

Prop 65 Notice

Distribution Block, High Conductive Al Body & Gas Filled Polycarbonate Insulator, #4 AWG- 500 kcmil (Run), #14 - 2/0 AWG (Tap), 380 Amps

Product Details

General

Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645567
UPC 12 Digit	7818106455677

Dimensions

Dimension - Height inch	3.55 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.58 in
Dimension - Width mm	66 mm

Electrical Ratings

Amperage Rating	380 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500
Conductor - AL Str Run Range	4-500
Conductor - AL Str Tap	4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	4-2/0
Conductor - Copper Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;500
Conductor - Copper Str Run Range	4-500
Conductor - Copper Str Tap	4;3;2;1;1/0;2/0
Conductor - Copper Str Tap Range	4-2/0

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	18 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)