



BDALHC22500

by Burndy
Catalog ID: BDALHC22500

Prop 65 Notice

Versipole, AWG 4 - 500 kcmil (Run), AWG 4 - 500 kcmil (Tap).

Provided capability to create as many poles as required, Up to 30 tap conductor accommodated

Product Details

General

Application	Industrial control feeder, HVAC system and wire ways
Installation Torque Recommended in-lb	500 in-lb
Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDA
UPC	781810645598
UPC 12 Digit	7818106455988

Dimensions

Dimension - Height inch	3.55 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.58 in
Dimension - Width mm	66 mm

Electrical Ratings

Amperage Rating	760 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500
Conductor - AL Str Run Range	4-500
Conductor - AL Str Tap	4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500
Conductor - AL Str Tap Range	4-500
Conductor - Copper Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;500
Conductor - Copper Str Run Range	4-500

Conductor - Copper Str Tap	4;3;2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;500
Conductor - Copper Str Tap Range	4-500

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	18 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)