



## BDALHC24500

by Burndy  
Catalog ID: BDALHC24500

Prop 65 Notice

Versipole, AWG 4 - 500 kcmil (Run), AWG 6 - 4/0 (Tap).

Provided capability to create as many poles as required, Up to 30 tap conductor accommodated

## Product Details

### General

Application	Industrial control feeder, HVAC system and wire ways
Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDA
UPC	781810645604
UPC 12 Digit	7818106456044

### Dimensions

Dimension - Height inch	3.55 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.58 in
Dimension - Width mm	66 mm

### Electrical Ratings

Amperage Rating	760 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500
Conductor - AL Str Run Range	4-500
Conductor - AL Str Tap	6;4;3;2;1;1/0;2/0;3/0;4/0
Conductor - AL Str Tap Range	6-4/0
Conductor - Copper Str Run	4;3;2;1;1/0;2/0;3/0;4/0;250;300;350;400;450;500
Conductor - Copper Str Run Range	4-500

Conductor - Copper Str Tap	6;5;4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Tap Range	6-4/0

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	18 EA
Minimum Pack Quantity	1

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)