



BDALHCEB

by Burndy
Catalog ID: BDALHCEB

Prop 65 Notice

Large End Barrier.

Product Details

General

| | |
|--------------------|---------------|
| Insulation | Y |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Temperature Rating | 194° F |
| Trade Name | VERSIPOLE™ |
| UPC | 781810646205 |
| UPC 12 Digit | 7818106462055 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 3.55 in |
| Dimension - L Length Overall mm | 145 mm |
| Dimension - Length Overall inch | 5.70 in |
| Dimension - Width inch | 0.15 in |
| Dimension - Width mm | 4 mm |

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|--------|
| Carton Quantity | 600 EA |
| Minimum Pack Quantity | 1 |

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)