



## BDAMHC11350

by Burndy  
Catalog ID: BDAMHC11350

Prop 65 Notice

310 Amp/Pole, #6 AWG - 350 kcmil Run & Tap.

### Product Details

#### General

|                                       |               |
|---------------------------------------|---------------|
| Installation Torque Recommended in-lb | 275 in-lb     |
| Insulation                            | Y             |
| Material                              | Aluminum      |
| Number Of Poles                       | Adder         |
| Plated                                | N             |
| Plating Type                          | Tin           |
| Temperature Rating                    | 194° F        |
| Trade Name                            | VERSIPOLE™    |
| UPC                                   | 781810646229  |
| UPC 12 Digit                          | 7818106462299 |

#### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 3.25 in |
| Dimension - L Length Overall mm | 127 mm  |
| Dimension - Length Overall inch | 5.00 in |
| Dimension - Width inch          | 1.72 in |
| Dimension - Width mm            | 44 mm   |

#### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Amperage Rating          | 310 A |
| Rating - Minimum Voltage | 600   |

#### Conductor Related

|                                  |   |
|----------------------------------|---|
| Conductor - AL Str Run           | 6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350 |
| Conductor - AL Str Run Range     | 6-350   |
| Conductor - AL Str Tap           | 6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350 |
| Conductor - AL Str Tap Range     | 6-350   |
| Conductor - Copper Str Run       | 6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350           |
| Conductor - Copper Str Run Range | 6-350   |
| Conductor - Copper Str Tap       | 6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350           |
| Conductor - Copper Str Tap Range | 6-350   |

#### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

## Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 18 EA |
| Minimum Pack Quantity | 1     |

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)