



## BDAMHC162/0

by Burndy  
Catalog ID: BDAMHC162/0

Prop 65 Notice

DIST BLK 2/0-14R 14-2T.

## Product Details

### General

Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810646243
UPC 12 Digit	7818106462433

### Dimensions

Dimension - Height inch	3.25 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	1.72 in
Dimension - Width mm	44 mm

### Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;5;4;3;2
Conductor - AL Str Tap Range	12-2
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2
Conductor - Copper Str Tap Range	14-2

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	18 EA
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)