



BDAMHCEB

by Burndy
Catalog ID: BDAMHCEB

Prop 65 Notice

DIST BLK MED END BARRIER.

Product Details

General

Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810646281
UPC 12 Digit	7818106462811

Dimensions

Dimension - Height inch	3.25 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)