



BDASHC112/01

by Burndy
Catalog ID: BDASHC112/01

Prop 65 Notice

Terminal Block, 3.08 in L, .93 in W, Glass Filled Ploycarbonate, AWG 14 - 2/0 (Run), AWG 14 - 2/0 (Tap).

Provided capability to create as many poles as required; Up to 30 tap conductor accommodated

Product Details

General

Application	Industrial control feeder, HVAC system and wire ways
Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDA
UPC	781810645475
UPC 12 Digit	7818106454755

Dimensions

Dimension - Height inch	2.81 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.08 in
Dimension - Width inch	0.93 in
Dimension - Width mm	24 mm

Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	12-2/0
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0

Conductor - Copper Str Tap Range	14-2/0
----------------------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	36 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)