

## BDBLCS3KA

by Burndy  
Catalog ID: BDBLCS3KA

Prop 65 Notice

Distribution block, One pole Finger Safe 6 AWG-350 kcmil (Run).

Provides capability to create as many poles as required and Up to 30 tap conductors accommodated



## Product Details

### General

Application	VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	621945448872
UPC 12 Digit	6219454488722

### Dimensions

Dimension - Height inch	4.12
Dimension - L Length Overall mm	141
Dimension - Length Overall inch	5.54
Dimension - Width mm	77 mm

### Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

### Conductor Related

Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	14 AWG - 2/0 AWG
Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Conductor - Copper Str Tap Range	14 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)