

## BDBLCS4K3

by Burndy  
Catalog ID: BDBLCS4K3

Prop 65 Notice

Distribution block, Three pole Open Style 6 AWG-350 kcmil (Run) 14 -2/0 AWG (Tap).

Provides capability to create as many poles as required and Up to 30 tap conductors accommodated



## Product Details

### General

|                    |  |
|--------------------|--|
| Application        | VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications. |
| Insulation         | Y  |
| Material           | Aluminum   |
| Number Of Poles    | 3  |
| Plated             | Y  |
| Plating Type       | Tin  |
| Sub Brand          | VERSIPOLE  |
| Temperature Rating | 194° F   |
| Trade Name         | VERSIPOLE™   |
| Type               | BDB  |
| UPC                | 781810676172   |
| UPC 12 Digit       | 7818106761722  |

### Dimensions

|                                 |      |
|---------------------------------|------|
| Dimension - Height inch         | 4.15 |
| Dimension - L Length Overall mm | 231  |
| Dimension - Length Overall inch | 9.09 |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Amperage Rating          | 620 A |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 600 V |

### Conductor Related

|                                  |  |
|----------------------------------|--|
| Conductor - AL Str Run Range     | 6 AWG - 350 kcmil  |
| Conductor - AL Str Tap Range     | 14 AWG - 2/0 AWG   |
| Conductor - Copper Str Run Range | 6 AWG - 350 kcmil  |
| Conductor - Copper Str Tap Range | 14 AWG - 2/0 AWG   |
| Conductor Type                   | <ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul> |

## Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - cULus              | Yes |
| Standards - RoHS Compliance Status | CM  |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)