



## BDBLCS5W1FS

by Burndy  
Catalog ID: BDBLCS5W1FS

Prop 65 Notice

Distribution block, One pole Finger Safe 4 AWG-500 Kcmil (Run), 4 AWG-500 Kcmil (Tap).

Provides capability to create as many poles as required and Up to 30 tap conductors accommodated

## Product Details

### General

Application	VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.
Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676486
UPC 12 Digit	7818106764866

### Dimensions

Dimension - Height inch	4.15
Dimension - L Length Overall mm	83
Dimension - Length Overall inch	3.25

### Electrical Ratings

Amperage Rating	380 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

### Conductor Related

Conductor - AL Str Run Range	4 AWG - 500 kcmil
Conductor - AL Str Tap Range	4 AWG - 500 kcmil
Conductor - Copper Str Run Range	4 AWG - 500 kcmil
Conductor - Copper Str Tap Range	4 AWG - 500 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)