

## BDBLHC163501

by Burndy  
Catalog ID: BDBLHC163501

Prop 65 Notice

Terminal block covers, AWG 6 - 350 kcmil (Run), AWG 14 - 2/0 (Tap),  
Power Distribution Block



## Product Details

### General

Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645833
UPC 12 Digit	7818106458333

### Dimensions

Dimension - Height inch	3.55
Dimension - L Length Overall mm	69
Dimension - Length Overall inch	2.73
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

### Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350
Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	14-2/0
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	4;3;2;1;1/0;2/0
Conductor - Copper Str Tap Range	14-2/0

Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>
----------------	---

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	18 EA
Minimum Pack Quantity	1

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)