



BDBLHC163503

by Burndy
Catalog ID: BDBLHC163503

Prop 65 Notice

Terminal block covers, AWG 6 - 350 kcmil (Run), AWG 14 - 2/0 (Tap),
Power Distribution Block

Provided capability to create as many poles as required, Up to 30 tap
conductor accommodated

Product Details

General

Application	Industrial control feeder, HVAC system and wire ways
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810645857
UPC 12 Digit	7818106458577

Dimensions

Dimension - Height inch	3.55
Dimension - L Length Overall mm	200
Dimension - Length Overall inch	7.89
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350
Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	14-2/0
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	4;3;2;1;1/0;2/0

Conductor - Copper Str Tap Range	14-2/0
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)