



BDBLHC263503

by Burndy
Catalog ID: BDBLHC263503

Prop 65 Notice

Power Distribution Block, AWG 6 - 350 kcmil (Run), AWG 14 - 2/0 (Tap)

Provided capability to create as many poles as required, Up to 30 tap conductor accommodated

Product Details

General

| | |
|--------------------|--|
| Application | Industrial control feeder, HVAC system and wire ways |
| Insulation | Y |
| Material | Aluminum |
| Number Of Poles | 3 |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | VERSI-POLE |
| Temperature Rating | 194° F |
| Trade Name | VERSIPOLE™ |
| Type | BDB |
| UPC | 781810646076 |
| UPC 12 Digit | 7818106460766 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 3.55 |
| Dimension - L Length Overall mm | 200 |
| Dimension - Length Overall inch | 7.89 |
| Dimension - Width inch | 5.70 in |
| Dimension - Width mm | 145 mm |

Electrical Ratings

| | |
|--------------------------|-------|
| Amperage Rating | 620 A |
| Rating - Minimum Voltage | 600 |

Conductor Related

| | |
|----------------------------------|---|
| Conductor - AL Str Run | 6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350 |
| Conductor - AL Str Run Range | 6-350 |
| Conductor - AL Str Tap | 12;10;8;6;4;3;2;1;1/0;2/0 |
| Conductor - AL Str Tap Range | 14-2/0 |
| Conductor - Copper Str Run | 6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350 |
| Conductor - Copper Str Run Range | 6-350 |
| Conductor - Copper Str Tap | 14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0 |

| | |
|----------------------------------|--|
| Conductor - Copper Str Tap Range | 14-2/0 |
| Conductor Type | <ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 6 EA |
| Minimum Pack Quantity | 1 |

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)