



BDBMCS5F2FS

by Burndy
Catalog ID: BDBMCS5F2FS

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.

Product Details

General

Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810676790
UPC 12 Digit	7818106767900

Dimensions

Height	4.52 in
Length	5.71 in

Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)