



BDBSCSCOVER

by Burndy
Catalog ID: BDBSCSCOVER

Hinged small cover for distribution block.

Ideal for current distribution to multiple locations, Provides maximum versatility, 600 V, AL9CU rated, Meets or exceeds industry standard requirements

Product Details

General

Application	For Use On: Suitable for use with aluminum or copper conductors
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	Terminal Block Covers
UPC	621945449343
UPC 12 Digit	6219454493433

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)