



BDTIBB

by Burndy
Catalog ID: BDTIBB

Bondit Wall Mount, #14 - #2 AWG, 4.01 in L, .71 in W.

Features: Meets Intersystem Bonding Requirements: NEC2008 250.94, One Connector Does It All, House Mount Or Meter Socket Mount, Incorporates Proven BURNDY SERVIT POST Design, Stainless Steel Set Screws, Accepts Main Ground Wire (#2 - #8), Up To 4 Intersystem Wires (#6 - #14), Easily Mounts To Meter Box During New Installation Or Can Be Wall Mounted, Easy To Follow Instructions Included, Does Not Damage Meter Socket, No Worries About Damaging The Paint Or Voiding Warranties, Easily Installed With A Wrench And Screwdriver, Open Design Prevents Buildup Of Hornets, Bees, Spiders, Mounting: House Or Meter Socket

Product Details

General

Application	Used to tying all of the system grounds together in one location
Sub Brand	BONDIT
Trade Name	BONDIT®
Type	BDT
UPC	781810504017
UPC 12 Digit	7818105040177

Dimensions

Dimension - Height inch	0.91 in
-------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)