



BE10TNCG1

by Burndy
Catalog ID: BE10TNCG1

Prop 65 Notice

Tinned copper flexible braid 10"x1.5"x0.17"

Product Details

General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810420737
UPC 12 Digit	7818104207377

Dimensions

Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10.00 in
Dimension - Width inch	1.5
Dimension - Width mm	38 mm
Weight	0.7 lb

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	340

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)