

## BE120NTN

by Burndy  
Catalog ID: BE120NTN

Prop 65 Notice

Tin Plated Ferrules



## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810279854
UPC 12 Digit	7818102798544

### Dimensions

Dimension - L Length Overall mm	3048 mm
Dimension - Length Overall inch	120.00 in

### Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)