



## BE12TN

by Burndy  
Catalog ID: BE12TN

Tin Plated Ferrules

### Product Details

#### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	621945334366
UPC 12 Digit	6219453343666

#### Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in

#### Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

#### Certifications and Compliance

Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)